

JK120

100A 20 Way A Board

Architecture

| | |
|-------------|------------------|
| Fixing mode | surface-mounting |
|-------------|------------------|

Main electrical features

| | |
|---------------|-------|
| Rated current | 100 A |
|---------------|-------|

Dimensions

| | |
|----------------------------|--------|
| Depth of installed product | 125 mm |
|----------------------------|--------|

| | |
|-----------------------------|--------|
| Height of installed product | 236 mm |
|-----------------------------|--------|

| | |
|----------------------------|--------|
| Width of installed product | 505 mm |
|----------------------------|--------|

Capacity

| | |
|-------------------|----|
| Number of modules | 20 |
|-------------------|----|

Cover, door

| | |
|----------------------|-------------------|
| Type of door closing | Quarter turn lock |
|----------------------|-------------------|

| | |
|---------------|-----|
| Interlockable | Yes |
|---------------|-----|

Materials

| | |
|-------------------|-------|
| Colour | beige |
| RAL colour number | 7035 |
| Material | Steel |

Equipment

| | |
|---------------------|----|
| Number of rows | 1 |
| Can be accessorized | No |

Standards

| | |
|-------------------------|-----------|
| European directive WEEE | concerned |
|-------------------------|-----------|

Safety

| | |
|---------------------|--------------|
| Protection index IP | IP2XC |
| Protection class | isol.class I |