

NRN232

MCB 2P 20kA C-32A 2M

:hager

- Architecture
 - Neutral position without neutral
 - Number of poles 2 P
 - Type of pole 2 P
 - Fixing mode Din-Rail
 - Curve C
- Main electrical features
 - Rated current 32 A
 - Type of supply voltage AC
- Voltage
 - Rated insulation voltage 500 V
 - Max operating voltage 415 V
 - Rated impulse withstand voltage 6000 V
- Electric current
 - Rated service breaking capacity Ics AC according IEC 60898-1 7.5 kA
 - Rated service breaking capacity Ics under 400V AC according IEC 60947-2

7.5 kA

- Dimensions
 - Depth of installed product
70 mm
 - Height of installed product
83 mm
 - Width of installed product
35 mm
- Power
 - Total power loss under IN
8 W
- Endurance
 - Electric endurance in number of cycles
4000
 - Number of mechanical operations
20000
- Capacity
 - Number of modules
2
- Installation, mounting
 - Tightening torque
2,8Nm
- Equipment
 - Can be accessorized
Yes
- Standards
 - Standard text
IEC 60947-2
 - European directive WEEE
concerned
- Safety
 - Protection index IP
IP20
- Use conditions
 - Storage temperature
-25/80 °C
- Temperature
 - Operating temperature
-25/70 °C