

VML310H

Consumer unit, Design 10, 10way, 100A, 30mA, RCCB in comer



Architecture

Fixing mode	surface-mounting
-------------	------------------

Main electrical features

Rated current	100 A
---------------	-------

Dimensions

Depth of installed product	98.2 mm
----------------------------	---------

Height of installed product	245 mm
-----------------------------	--------

Width of installed product	297 mm
----------------------------	--------

Capacity

Number of modules	10
-------------------	----

Cover, door

Type of door closing	non keylock
----------------------	-------------

Interlockable	No
---------------	----

Materials

RAL colour number	9010
-------------------	------

Material	Steel
----------	-------

Equipment

Number of rows	1
----------------	---

Can be accessorized	No
---------------------	----

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

Protection index IP	IP2XC
---------------------	-------

Protection class	Protection class III
------------------	----------------------