



### Switch h1600 4P 1250A

#### Technical Characteristics

Neutral position	left
Number of poles	4 P
Type of pole	4 P
Rated operational voltage Ue	690 V 220 V
Frequency	50/60 Hz
Rated current	1250 A
Rated insulation voltage	800 V
Rated impulse withstand voltage	8000 V
Total power loss under IN	187.5 W
Electric endurance in number of cycles	4500
Number of mechanical operations	15000
Interlockable	Yes
Tightening torque	65Nm
Connection cross-sect. flexible conductor	3x240mm <sup>2</sup>
Connection cross-sect. rigid cable	3x240mm <sup>2</sup>
Type of connection	Terminal
Can be accessorized	No
Standard text	IEC 60947-3
European directive WEEE	concerned
Protection index IP	IP4X
Operating temperature	70 °C -25 °C