



ACB106

## RCBO Electronic 1M 1P 10kA B-6A 10mA AC Class

### Technical characteristics

#### Architecture

Neutral position	right
Number of poles	1 P
Type of pole	1 P
Curve	B

#### Main electrical features

Rated operational voltage Ue	230 / 240 V
Frequency	50 Hz

#### Voltage

Rated insulation voltage	250 V
Max operating voltage	253 V
Rated impulse withstand voltage	4000 V

#### Electric current

Rated residual operating current	10 mA
Rated short circuit breaking capacity Icn under 230V AC according IEC60898-1	10 kA

#### Electric current / temperature

Rating current 30°C	6 A
---------------------	-----

#### Dimensions

Depth of installed product	73 mm
Height of installed product	115 mm
Width of installed product	17.8 mm

#### Power

Total power loss under IN	1.5 W
---------------------------	-------

#### Endurance

Electric endurance in number of cycles	2000
Number of mechanical operations	1000

#### Installation, mounting

Tightening torque	2,1Nm
-------------------	-------

#### Standards

Standard text	IEC 61009-1 ; EN 61009-1
European directive WEEE	concerned

**Safety**

Protection index IP	IP20
Residual current type	AC