



ADC816F



## RCBO 1P+N 4.5kA C-16A 30mA AC Class

### Technical characteristics

#### Architecture

Neutral position	left
Number of poles	2 P
Curve	C

#### Main electrical features

Rated operational voltage $U_e$	240 V
Frequency	50 Hz

#### Voltage

Rated insulation voltage	500 V
Max operating voltage	0 V
Rated impulse withstand voltage	4 kV

#### Electric current

Rated residual operating current	30 mA
Rated short circuit breaking capacity $I_{cn}$ under 230V AC according IEC60898-1	4.5 kA

#### Electric current / temperature

Rating current 30°C	16 A
---------------------	------

#### Dimensions

Depth of installed product	68 mm
Height of installed product	0 mm
Width of installed product	0 mm

#### Power

Total power loss under $I_N$	5.2 W
------------------------------	-------

#### Tripping

Short-time delayed tripping	No
-----------------------------	----

#### Endurance

Electric endurance in number of cycles	0
Number of mechanical operations	0

#### Connection

Connection cross-sect. flexible conductor	1,5 bis 95mm <sup>2</sup>
Connection cross-sect. rigid cable	1,5 to 95mm <sup>2</sup>

#### Standards

---

European directive WEEE

concerned

**Safety**

---

Protection index IP

IP2X

---

Residual current type

AC

**Use conditions**

---

Operating temperature

-25...40 °C