



ADC820F



**RCBO 1P+N 4.5kA C-20A 30mA AC Class**

**Technical characteristics**

**Architecture**

Neutral position	left
Number of poles	2 P
Type of pole	1P+N
Curve	C

**Main electrical features**

Rated operational voltage $U_e$	240 V
Frequency	50 Hz

**Voltage**

Rated insulation voltage	500 V
Max operating voltage	240 V
Rated impulse withstand voltage	4000 V

**Electric current**

Rated residual operating current	30 mA
Rated short circuit breaking capacity $I_{cn}$ under 230V AC according IEC60898-1	4.5 kA

**Electric current / temperature**

Rating current 30°C	20 A
---------------------	------

**Dimensions**

Depth of installed product	68 mm
Height of installed product	83 mm
Width of installed product	35 mm

**Power**

Total power loss under $I_N$	6.6 W
------------------------------	-------

**Tripping**

Short-time delayed tripping	No
-----------------------------	----

**Endurance**

Electric endurance in number of cycles	2000
Number of mechanical operations	2000

**Installation, mounting**

Tightening torque	2,1Nm
-------------------	-------

**Connection**

Connection cross-sect. flexible conductor	1 / 16mm <sup>2</sup>
Connection cross-sect. rigid cable	1 / 25mm <sup>2</sup>
Type of connection	with screw

---

**Standards**

Standard text	EN 61009-1
---------------	------------

---

**Safety**

Residual current type	AC
-----------------------	----

---

**Use conditions**

Operating temperature	-25...40 °C
-----------------------	-------------