



ARC975U

MCB with dangerous arc detection 1P+N 6kA C-25A 2M

Technical characteristics

Architecture

Neutral position	right
Number of poles	2 P
Type of pole	1P+N
Curve	C

Main electrical features

Rated operational voltage Ue	230 V
Type of supply voltage	AC

Voltage

Rated insulation voltage	500 V
Max operating voltage	253 V
Rated impulse withstand voltage	4 kV

Electric current

Rated service breaking capacity Ics AC according IEC 60898-1	6 kA
Rated short circuit breaking capacity Icn under 230V AC according IEC60898-1	6 kA

Electric current / temperature

Rating current 30°C	25 A
---------------------	------

Dimensions

Depth of installed product	70 mm
Height of installed product	85 mm
Width of installed product	35.5 mm

Power

Total power loss under IN	6.48 W
---------------------------	--------

Endurance

Electric endurance in number of cycles	2000
Number of mechanical operations	4000

Installation, mounting

Tightening torque	2Nm
-------------------	-----

Accessories included

Type of accessory	AFDD
-------------------	------

Equipment	
Quick connect	no
Can be accessorized	Yes
Standards	
Standard text	EN 62606 ; IEC 60898-1
European directive WEEE	concerned
Safety	
Protection index IP	IP20
Use conditions	
Operating temperature	-25...60 °C