



ADA325G

**RCBO Electronic 1P 6kA B Curve -25A, 30mA Type A(AC & Pulsating DC Sensitive)1M**

**Technical characteristics**

**Architecture**

Type of pole	1P
Curve	B

**Electric current**

Rated current	25 A
Rated residual operating current I <sub>dn</sub>	30 mA
Rated current -25°C	32.34 A
Rated current at -20°C	31.79 A
Rated current -15°C	31.24 A
Rated current -10°C	31.13 A
Rated current -5°C	30.15 A
Rated current at 0°C	29.60 A
Rated current 5°C	29.05 A
Rated current 10°C	28.50 A
Rated current 15°C	27.96 A
Rated current at 20°C	27.41 A
Rated current 25°C	26.86 A
Rated current 30°C	25 A
Rated current 35°C	25.77 A
Rated current at 40°C	25.22 A
Rated current at 50°C	25 A
Rated current 55°C	23.58 A
Rated current 60°C	23.03 A
Correction factor of rating current for 2 devices placed side by side	0.95
Correction factor of rating current for 3 devices placed side by side	0.95
Correction factor of rating current for 4 and 5 devices placed side by side	0.90
Correction factor of rating current for 6 devices placed side by side	0.85
Min./max. threshold value of the AC thermal operation	1.13 - 1.45 A

**Safety**

Residual current type	A
Ingress Protection (IP) class	IP20

**Main electrical attributes**

### Voltage

Rated insulation voltage U <sub>i</sub>	250 V
Rated impulse withstand voltage U <sub>imp</sub>	4,000 V
Max. operating voltage	253 V
Rated operational voltage U <sub>e</sub>	230 - 230 V
Overtoltage category according to IEC 60947-1	3

### Power

Total power loss under I <sub>N</sub>	5.91 W
---------------------------------------	--------

### Frequency

Frequency	50 - 50 Hz
-----------	------------

### Use conditions

Max. Altitude	2,000 m
Class of energy limitation I <sup>2</sup> t	3
Operating temperature	-20 - 70 °C
Storage/transport temperature	-25 - 80 °C

### Endurance

Electric endurance in number of cycles	16,000
Number of mechanical operations	20,000

### Connection

Cross-section of input with screws, for flexible conductors	1 - 10 mm <sup>2</sup>
Cross-section of input with screws, for massive conductors	1 - 16 mm <sup>2</sup>

### Installation, mounting

Type of top connection for modular devices	Screw terminal
Type of bottom connection for modular devices	Screw terminal

### Capacity

Number of modules	1
-------------------	---

### Dimensions

Height	92 mm
Width	17.70 mm
Depth	70 mm

### Compatibility

Suitable for DIN Rail	Yes
-----------------------	-----