



ARL925U

**RCBO with dangerous arc detection 1M 25A B curve 6kA Type A 30mA LFL 1m**

**Technical characteristics**

**Electric current**

Rated current	25 A
Rated current -25°C	32.4 A
Rated current at -20°C	31.7 A
Rated current -15°C	31.1 A
Rated current -10°C	30.4 A
Rated current -5°C	29.7 A
Rated current at 0°C	29 A
Rated current 5°C	28.4 A
Rated current 10°C	27.7 A
Rated current 15°C	27 A
Rated current at 20°C	26.3 A
Rated current 25°C	25.7 A
Rated current 30°C	25 A
Rated current 35°C	24.3 A
Rated current at 40°C	23.7 A
Rated current at 45°C	23 A
Rated current at 50°C	22.3 A
Rated current 55°C	21.6 A
Rated current 60°C	21 A
Rated current 65°C	20.3 A
Rated current 70°C	19.6 A
Rated short-circuit breaking capacity $I_{cn}$ under 230 V AC according to IEC 61009-1	6 kA
Breaking and opening capacity $I_{dm}$	3 kA
Rated residual operating current $I_{dn}$	30 mA

**Architecture**

Curve	B
Type of pole	1P+N

**Installation, mounting**

Nominal tightening torque top terminal	2.40 - 2.40 Nm
Nominal tightening torque down terminal	3.50 - 3.50 Nm
Type of bottom connection for modular devices	biconnect
Type of top connection for modular devices	Screw terminal

**Main electrical attributes**

Rated short-circuit breaking capacity I <sub>cn</sub> AC according to IEC 60898-1	6 kA
---	------

#### Safety

Residual current type	A
-----------------------	---

#### Voltage

Rated insulation voltage U <sub>i</sub>	400 V
Rated impulse withstand voltage U <sub>imp</sub>	4,000 V
Rated operational voltage U <sub>e</sub>	230 - 230 V

#### Power

Total power loss under I <sub>N</sub>	8.3 W
---------------------------------------	-------

#### Use conditions

Class of energy limitation I <sup>2</sup> t	3
Operating temperature	-25 - 70 °C
Storage/transport temperature	-25 - 80 °C

#### Endurance

Number of mechanical operations	8,000
Electric endurance in number of cycles	2,000

#### Capacity

Number of modules	1
-------------------	---

#### Dimensions

Height	125 mm
Width	17.50 mm
Depth	70 mm

#### Frequency

Frequency	50 - 50 Hz
-----------	------------