



ADA332G

RCBO Electronic 1P 6kA B Curve -32A, 30mA Type A(AC & Pulsating DC Sensitive)1M

Technical characteristics

Architecture

Neutral position	right
Number of poles	1 P
Type of pole	1 P
Fixing mode	DIN rail type O (symmetrical)

Main electrical features

Rated operational voltage Ue	230 V
Frequency	50 Hz
Type of supply voltage	AC

Voltage

Rated insulation voltage	250 V
Max operating voltage	253 V
Rated impulse withstand voltage	4000 V

Electric current

Rated residual operating current	30 mA
Rated short circuit breaking capacity Icn under 230V AC according IEC60898-1	6 kA

Electric current / temperature

Rating current 30°C	32 A
---------------------	------

Dimensions

Depth of installed product	70 mm
Height of installed product	92 mm
Width of installed product	17.7 mm

Power

Total power loss under IN	7.08 W
---------------------------	--------

Endurance

Electric endurance in number of cycles	16000
Number of mechanical operations	20000

Equipment

Quick connect	no
Can be accessorized	No

Standards

European directive WEEE

concerned

Safety

Protection index IP

IP20

Residual current type

A

Use conditions

Operating temperature

-20...70 °C