



ARM906U

MCB with dangerous arc detection 1M 6A B curve 6kA

Technical characteristics

Architecture

Neutral position	right
Number of poles	2 P
Type of pole	1P+N
Curve	B

Main electrical features

Rated operational voltage Ue	230 V
Type of supply voltage	AC

Voltage

Rated insulation voltage	400 V
Max operating voltage	253 V
Rated impulse withstand voltage	4 kV

Electric current

Rated service breaking capacity Ics AC according IEC 60898-1	6 kA
Rated short circuit breaking capacity Icn under 230V AC according IEC60898-1	6 kA

Electric current / temperature

Rating current 30°C	6 A
---------------------	-----

Dimensions

Depth of installed product	70 mm
Height of installed product	125 mm
Width of installed product	17.5 mm

Power

Total power loss under IN	2.59 W
---------------------------	--------

Endurance

Electric endurance in number of cycles	2000
Number of mechanical operations	8000

Equipment

Quick connect	no
Can be accessorized	No

Standards

Standard text	EN 62606 ; EN 60898-1
---------------	-----------------------

Use conditions

Operating temperature

-25...70 °C