



ARM932U

**MCB with dangerous arc detection 1M 32A B curve 6kA**

**Technical characteristics**

**Architecture**

Neutral position	right
Number of poles	2 P
Type of pole	1P+N
Curve	B

**Main electrical features**

Rated operational voltage Ue	230 V
Type of supply voltage	AC

**Voltage**

Rated insulation voltage	400 V
Max operating voltage	253 V
Rated impulse withstand voltage	4 kV

**Electric current**

Rated service breaking capacity Ics AC according IEC 60898-1	6 kA
Rated short circuit breaking capacity Icn under 230V AC according IEC60898-1	6 kA

**Electric current / temperature**

Rating current 30°C	32 A
---------------------	------

**Dimensions**

Depth of installed product	70 mm
Height of installed product	125 mm
Width of installed product	17.5 mm

**Power**

Total power loss under IN	9.44 W
---------------------------	--------

**Endurance**

Electric endurance in number of cycles	2000
Number of mechanical operations	8000

**Equipment**

Quick connect	no
Can be accessorized	No

**Standards**

Standard text	EN 62606 ; EN 60898-1
---------------	-----------------------

**Use conditions**

---

Operating temperature

-25...70 °C