



ADA970U

**RCBO 1P+N 6kA C-20A 30mA A Class**

**Technical characteristics**

**Architecture**

Neutral position	right
Number of poles	2 P
Type of pole	1P+N
Curve	C

**Main electrical features**

Rated operational voltage U <sub>e</sub>	240 V
Frequency	50 Hz

**Voltage**

Rated insulation voltage	500 V
Max operating voltage	240 V
Rated impulse withstand voltage	4000 V

**Electric current**

Rated residual operating current	30 mA
Rated short circuit breaking capacity I <sub>cn</sub> under 230V AC according IEC60898-1	6 kA

**Electric current / temperature**

Rating current 30°C	20 A
---------------------	------

**Dimensions**

Depth of installed product	68 mm
Height of installed product	83 mm
Width of installed product	35 mm

**Power**

Total power loss under I <sub>N</sub>	6.6 W
---------------------------------------	-------

**Endurance**

Electric endurance in number of cycles	2000
Number of mechanical operations	2000

**Installation, mounting**

Tightening torque	2,1Nm
-------------------	-------

**Connection**

Connection cross-sect. flexible conductor	1 / 16mm <sup>2</sup>
Connection cross-sect. rigid cable	1 / 25mm <sup>2</sup>

Type of connection	with screw
<b>Standards</b>	
Standard text	IEC 61009-1
European directive WEEE	concerned
<b>Safety</b>	
Protection index IP	IP20
Residual current type	A
<b>Use conditions</b>	
Operating temperature	-25...40 °C