



ARR925U

**RCBO with dangerous arc detection 1M 25A B curve 6kA Type A 30mA**

**Technical characteristics**

**Architecture**

Neutral position	right
Number of poles	2 P
Type of pole	1P+N
Fixing mode	DIN rail type O (symmetrical)
Curve	B

**Main electrical features**

Rated operational voltage Ue	230 V
Type of supply voltage	AC

**Voltage**

Rated insulation voltage	400 V
Max operating voltage	253 V
Rated impulse withstand voltage	4 kV

**Electric current**

Rated residual operating current	30 mA
----------------------------------	-------

**Electric current / temperature**

Rating current 30°C	25 A
---------------------	------

**Dimensions**

Depth of installed product	70 mm
Height of installed product	125 mm
Width of installed product	17.5 mm

**Power**

Total power loss under IN	6.45 W
---------------------------	--------

**Endurance**

Electric endurance in number of cycles	2000
Number of mechanical operations	8000

**Accessories included**

Type of accessory	AFDD
-------------------	------

**Equipment**

Quick connect	no
Can be accessorized	No

**Standards**

---

Standard text	EN 62606 ; EN 61009-1
European directive WEEE	concerned

---

**Safety**

---

Protection index IP	IP20
Residual current type	A

---

**Use conditions**

---

Operating temperature	-25...70 °C
-----------------------	-------------

---