



BDA263

Earth leakage add-on block 2P 63A 30mA A Class

Technical characteristics

Architecture

Neutral position	right
Number of poles	2 P
Type of pole	2 P

Main electrical features

Rated operational voltage Ue	230 V
Frequency	50 Hz

Voltage

Rated insulation voltage	500 V
Rated impulse withstand voltage	4000 V

Electric current

Rated residual operating current	30 mA
----------------------------------	-------

Dimensions

Depth of installed product	92 mm
Height of installed product	70 mm
Width of installed product	4.4 cm

Power

Total power loss under IN	18 W
---------------------------	------

Tripping

Short-time delayed tripping	No
-----------------------------	----

Endurance

Electric endurance in number of cycles	1000
Number of mechanical operations	1000

Installation, mounting

Tightening torque	2,9Nm
-------------------	-------

Connection

Connection cross-sect. flexible conductor	16mm ²
Connection cross-sect. rigid cable	25mm ²

Standards

Standard text	EN 61009-1
---------------	------------

Safety

Use conditions

Operating temperature

-25...70 °C