



BE163T

Earth leakage add-on-block 3P 63A 100mA A Class 1mod Electronic

Technical characteristics

Architecture

| | |
|------------------|-------|
| Neutral position | right |
| Number of poles | 3 P |

Main electrical features

| | |
|------------------------------|-------------|
| Rated operational voltage Ue | 240 / 415 V |
| Frequency | 50 Hz |

Voltage

| | |
|---------------------------------|--------|
| Rated insulation voltage | 500 V |
| Rated impulse withstand voltage | 4000 V |

Electric current

| | |
|----------------------------------|--------|
| Rated residual operating current | 100 mA |
|----------------------------------|--------|

Power

| | |
|---------------------------|-------|
| Total power loss under IN | 3.2 W |
|---------------------------|-------|

Endurance

| | |
|--|------|
| Electric endurance in number of cycles | 1000 |
| Number of mechanical operations | 1000 |

Installation, mounting

| | |
|-------------------|-------|
| Tightening torque | 3,5Nm |
|-------------------|-------|

Connection

| | |
|---|-------------------|
| Connection cross-sect. flexible conductor | 16mm ² |
|---|-------------------|

Standards

| | |
|-------------------------|-----------|
| European directive WEEE | concerned |
|-------------------------|-----------|

Safety

| | |
|-----------------------|------|
| Protection index IP | IP20 |
| Residual current type | A |

Use conditions

| | |
|-----------------------|------------|
| Operating temperature | -5...40 °C |
|-----------------------|------------|