



BF264

Earth leakage add-on block 2P 63A 300mA AC Class

Technical Characteristics

Architecture

| | |
|------------------|------|
| Neutral position | left |
| Number of poles | 2 P |
| Type of pole | 2 P |

Main electrical features

| | |
|------------------------------|-------------|
| Rated operational voltage Ue | 230 / 400 V |
| Frequency | 50 Hz |
| Rated current | 63 A |

Voltage

| | |
|---------------------------------|--------|
| Rated insulation voltage | 500 V |
| Rated impulse withstand voltage | 4000 V |

Electric current

| | |
|----------------------------------|--------|
| Rated residual operating current | 300 mA |
|----------------------------------|--------|

Dimensions

| | |
|-----------------------------|--------|
| Depth of installed product | 9.2 cm |
| Height of installed product | 7 cm |
| Width of installed product | 3.5 cm |

Power

| | |
|---------------------------|------|
| Total power loss under IN | 18 W |
|---------------------------|------|

Tripping

| | |
|-----------------------------|----|
| Short-time delayed tripping | No |
|-----------------------------|----|

Endurance

| | |
|--|------|
| Electric endurance in number of cycles | 2000 |
| Number of mechanical operations | 1000 |

Capacity

| | |
|-------------------|---|
| Number of modules | 2 |
|-------------------|---|

Installation, mounting

| | |
|-------------------|-------|
| Tightening torque | 2,8Nm |
|-------------------|-------|

Connection

| | |
|---|-------------------|
| Connection cross-sect. flexible conductor | 16mm ² |
| Connection cross-sect. rigid cable | 25mm ² |

Standards

| | |
|-------------------------|-----------|
| European directive WEEE | concerned |
|-------------------------|-----------|

Safety

| | |
|-----------------------|------|
| Protection index IP | IP20 |
| Residual current type | AC |

Use conditions

