



BFA263

Earth leakage add-on block 2P 63A 300mA A Class

Technical characteristics

Architecture

| | |
|------------------|-------------------------------|
| Neutral position | right |
| Number of poles | 2 P |
| Type of pole | 2 P |
| Fixing mode | DIN rail type O (symmetrical) |

Main electrical features

| | |
|------------------------------|-------------|
| Rated operational voltage Ue | 230 / 400 V |
| Frequency | 50 Hz |

Voltage

| | |
|---------------------------------|--------|
| Rated insulation voltage | 500 V |
| Rated impulse withstand voltage | 4000 V |

Electric current

| | |
|----------------------------------|--------|
| Rated residual operating current | 300 mA |
|----------------------------------|--------|

Dimensions

| | |
|-----------------------------|--------|
| Depth of installed product | 92 mm |
| Height of installed product | 70 mm |
| Width of installed product | 3.5 cm |

Power

| | |
|---------------------------|------|
| Total power loss under IN | 18 W |
|---------------------------|------|

Endurance

| | |
|--|------|
| Electric endurance in number of cycles | 2000 |
| Number of mechanical operations | 2000 |

Connection

| | |
|---|-------------------|
| Connection cross-sect. flexible conductor | 16mm ² |
|---|-------------------|

Standards

| | |
|-------------------------|------------|
| Standard text | EN 61009-1 |
| European directive WEEE | concerned |

Safety

| | |
|-----------------------|------|
| Protection index IP | IP2X |
| Residual current type | A |

Use conditions

