



BN264

Earth leakage add-on block 2P 63A 100mA AC S Class

Technical characteristics

Architecture

Neutral position	left
Number of poles	2 P

Main electrical features

Rated operational voltage Ue	230 / 400 V
Frequency	50 Hz

Voltage

Rated insulation voltage	500 V
Rated impulse withstand voltage	4000 V

Electric current

Rated residual operating current	100 mA
----------------------------------	--------

Dimensions

Depth of installed product	9.2 cm
Height of installed product	7 cm
Width of installed product	3.5 cm

Endurance

Electric endurance in number of cycles	2000
Number of mechanical operations	1000

Installation, mounting

Tightening torque	2,8Nm
-------------------	-------

Safety

Protection index IP	IP20
Residual current type	AC SEL

Use conditions

Operating temperature	-5...40 °C
-----------------------	------------