



ADC832F



RCBO 1P+N 4.5kA C-32A 30mA AC Class

Technical characteristics

Architecture

Neutral position	left
Number of poles	2 P
Curve	C

Main electrical features

Rated operational voltage U _e	240 V
Frequency	50 Hz

Voltage

Rated insulation voltage	500 V
Max operating voltage	240 V
Rated impulse withstand voltage	4 kV

Electric current

Rated residual operating current	30 mA
Rated short circuit breaking capacity I _{cn} under 230V AC according IEC60898-1	4.5 kA

Electric current / temperature

Rating current 30°C	32 A
---------------------	------

Dimensions

Depth of installed product	68 mm
Height of installed product	83 mm
Width of installed product	35 mm

Power

Total power loss under I _N	8.3 W
---------------------------------------	-------

Endurance

Electric endurance in number of cycles	2000
Number of mechanical operations	1000

Installation, mounting

Tightening torque	2,1Nm
-------------------	-------

Connection

Type of connection	with screw
--------------------	------------

Standards

Standard text	EN 61009-1
---------------	------------

Safety

Residual current type

AC

Use conditions

Operating temperature

-25...40 °C