



BNA263

Earth leakage add-on block 2P 63A 100mA A S Class

Technical characteristics

Architecture

Neutral position	right
Number of poles	2 P
Type of pole	2 P
Fixing mode	DIN rail type O (symmetrical)

Main electrical features

Rated operational voltage Ue	230 / 400 V
Frequency	50 Hz

Voltage

Rated insulation voltage	500 V
Rated impulse withstand voltage	4000 V

Electric current

Rated residual operating current	100 mA
----------------------------------	--------

Dimensions

Depth of installed product	92 mm
Height of installed product	70 mm
Width of installed product	3.5 cm

Endurance

Electric endurance in number of cycles	2000
Number of mechanical operations	1000

Connection

Connection cross-sect. flexible conductor	16mm ²
---	-------------------

Standards

Standard text	EN 61009-1
European directive WEEE	concerned

Safety

Protection index IP	IP2X
Residual current type	A SEL

Use conditions

Operating temperature	-25...70 °C
-----------------------	-------------