



AEC416U

RCBO 1M 1P 10kA C-16A 100mA A

Technical characteristics

Architecture

Neutral position	right
Number of poles	1 P
Type of pole	1 P
Curve	C

Main electrical features

Rated operational voltage Ue	230 / 240 V
Frequency	50/60 Hz
Type of supply voltage	AC

Voltage

Rated insulation voltage	250 V
Rated impulse withstand voltage	4000 V

Electric current

Rated residual operating current	100 mA
----------------------------------	--------

Electric current / temperature

Rating current 30°C	16 A
---------------------	------

Dimensions

Depth of installed product	70 mm
Height of installed product	115 mm
Width of installed product	17.8 mm

Power

Total power loss under IN	4.9 W
---------------------------	-------

Endurance

Electric endurance in number of cycles	2000
Number of mechanical operations	10000

Equipment

Quick connect	no
Can be accessorized	No

Standards

Standard text	BS 61009-1 ; EN 61009-1
---------------	-------------------------

Safety

Residual current type

A

Use conditions

Operating temperature

-25...40 °C