



BP264

Earth leakage add-on block 2P 63A 300mA AC S Class

Technical Characteristics

Architecture

Neutral position	left
Number of poles	2 P
Type of pole	2 P

Main electrical features

Rated operational voltage Ue	230 / 400 V
Frequency	50 Hz
Rated current	63 A

Voltage

Rated insulation voltage	500 V
Rated impulse withstand voltage	4000 V

Electric current

Rated residual operating current	300 mA
----------------------------------	--------

Dimensions

Depth of installed product	9.2 cm
Height of installed product	7 cm
Width of installed product	3.5 cm

Power

Total power loss under IN	4.4 W
---------------------------	-------

Tripping

Short-time delayed tripping	No
-----------------------------	----

Endurance

Electric endurance in number of cycles	2000
Number of mechanical operations	1000

Capacity

Number of modules	2
-------------------	---

Installation, mounting

Tightening torque	2,8Nm
-------------------	-------

Connection

Connection cross-sect. flexible conductor	16mm ²
Connection cross-sect. rigid cable	25mm ²

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

Protection index IP	IP20
Residual current type	AC SEL

Use conditions

