



ARC582U

## MCB with dangerous arc detection 1P+N 10kA C-32A 2M

### Technical characteristics

#### Electric current

Rated current	32 A
Rated current -25°C	38.30 A
Rated current at -20°C	37.77 A
Rated current -15°C	37.24 A
Rated current -10°C	36.69 A
Rated current -5°C	36.14 A
Rated current at 0°C	35.58 A
Rated current 5°C	35.01 A
Rated current 10°C	34.43 A
Rated current 15°C	33.84 A
Rated current at 20°C	33.24 A
Rated current 25°C	32.63 A
Rated current 30°C	32 A
Rated current 35°C	31.52 A
Rated current at 40°C	31.03 A
Rated current at 45°C	30.54 A
Rated current at 50°C	30.03 A
Rated current 55°C	29.52 A
Rated current 60°C	29 A

#### Architecture

Curve	C
Type of pole	1P+N

#### Main electrical attributes

Rated short-circuit breaking capacity I <sub>cn</sub> AC according to IEC 60898-1	10 kA
Nominal tightening torque top terminal	2 - 2 Nm
Nominal tightening torque down terminal	2 - 2 Nm

#### Voltage

Rated insulation voltage U <sub>i</sub>	500 V
Rated impulse withstand voltage U <sub>imp</sub>	4,000 V

#### Power

Total power loss under I <sub>N</sub>	8.31 W
---------------------------------------	--------

#### Use conditions

Class of energy limitation I <sup>2</sup> t	3
---	---

Operating temperature	-25 - 60 °C
Storage/transport temperature	-40 - 70 °C
<b>Endurance</b>	
Number of mechanical operations	4,000
Electric endurance in number of cycles	2,000
<b>Installation, mounting</b>	
Nominal tightening torque	2 - 2 Nm
Type of bottom connection for modular devices	biconnect
Type of top connection for modular devices	Screw terminal
<b>Capacity</b>	
Number of modules	2
<b>Dimensions</b>	
Height	85 mm
Width	35.50 mm
Depth	70 mm