



ARC932U

MCB with dangerous arc detection 1P+N 6kA B-32A 2M

Technical characteristics

Architecture

Neutral position	right
Number of poles	2 P
Type of pole	1P+N
Curve	B

Main electrical features

Rated operational voltage Ue	230 V
Type of supply voltage	AC

Voltage

Rated insulation voltage	500 V
Max operating voltage	253 V
Rated impulse withstand voltage	4 kV

Electric current

Rated service breaking capacity Ics AC according IEC 60898-1	6 kA
Rated short circuit breaking capacity Icn under 230V AC according IEC60898-1	6 kA

Electric current / temperature

Rating current 30°C	32 A
---------------------	------

Dimensions

Depth of installed product	70 mm
Height of installed product	85 mm
Width of installed product	35.5 mm

Power

Total power loss under IN	8.31 W
---------------------------	--------

Endurance

Electric endurance in number of cycles	2000
Number of mechanical operations	4000

Installation, mounting

Tightening torque	2Nm
-------------------	-----

Accessories included

Type of accessory	AFDD
-------------------	------

Equipment

Quick connect	no
Can be accessorized	Yes

Standards

Standard text	EN 62606 ; IEC 60898-1
European directive WEEE	concerned

Safety

Protection index IP	IP20
---------------------	------

Use conditions

Operating temperature	-25...60 °C
-----------------------	-------------