



CD285U

**RCCB 2P 100A 30mA A**

**Technical characteristics**

**Architecture**

Neutral position	right
Number of poles	2 P
Type of pole	1P+N
Fixing mode	DIN rail type O (symmetrical)

**Main electrical features**

Frequency	50 Hz
Type of supply voltage	AC

**Voltage**

Rated impulse withstand voltage	4000 V
---------------------------------	--------

**Electric current**

Rated residual operating current	30 mA
Rated conditional short-circuit current $I_{nc}$ according to EN 61008-1	6 kA

**Electric current / temperature**

Rating current 30°C	100 A
---------------------	-------

**Dimensions**

Depth of installed product	70 mm
Height of installed product	83 mm
Width of installed product	35 mm

**Power**

Total power loss under $I_N$	14.3 W
------------------------------	--------

**Tripping**

Short-time delayed tripping	No
-----------------------------	----

**Endurance**

Electric endurance in number of cycles	2000
Number of mechanical operations	4000

**Installation, mounting**

Tightening torque	3,3Nm
-------------------	-------

**Connection**

Type of connection	with screw
--------------------	------------

**Equipment**

---

Can be accessorized Yes

**Standards**

---

Standard text EN 61008-1

European directive WEEE concerned

**Safety**

---

Protection index IP IP20

Residual current type A

**Use conditions**

---

Operating temperature -25...40 °C