



CDB540E

RCCB 1P+N 40A 30mA B

Technical characteristics

Architecture

Neutral position	right
Number of poles	2 P
Type of pole	1P+N
Fixing mode	DIN rail type O (symmetrical)

Main electrical features

Rated operational voltage U _e	230 V
Frequency	50 Hz
Type of supply voltage	AC

Voltage

Rated insulation voltage	400 V
Max operating voltage	253 V
Rated impulse withstand voltage	4000 V

Electric current

Rated residual operating current	30 mA
Rated conditional short-circuit current I _{nc} according to EN 61008-1	10 kA

Electric current / temperature

Rating current 30°C	40 A
---------------------	------

Dimensions

Depth of installed product	70 mm
Height of installed product	85 mm
Width of installed product	72 mm

Power

Total power loss under I _N	3.31 W
---------------------------------------	--------

Tripping

Short-time delayed tripping	No
-----------------------------	----

Endurance

Electric endurance in number of cycles	10000
Number of mechanical operations	20000

Equipment

Can be accessorized	Yes
---------------------	-----

Standards

Standard text	EN 62423
European directive WEEE	concerned

Safety

Protection index IP	IP20
---------------------	------

Use conditions

Operating temperature	-25...70 °C
-----------------------	-------------