



ARL956U

RCBO with dangerous arc detection 1M 6A C curve 6kA Type A 30mA LFL 1m

Technical characteristics

Electric current

Rated current	6 A
Rated current -25°C	7.4 A
Rated current at -20°C	7.3 A
Rated current -15°C	7.1 A
Rated current -10°C	7 A
Rated current -5°C	6.9 A
Rated current at 0°C	6.8 A
Rated current 5°C	6.6 A
Rated current 10°C	6.5 A
Rated current 15°C	6.4 A
Rated current at 20°C	6.3 A
Rated current 25°C	6.1 A
Rated current 30°C	6 A
Rated current 35°C	5.9 A
Rated current at 40°C	5.7 A
Rated current at 45°C	5.6 A
Rated current at 50°C	5.5 A
Rated current 55°C	5.4 A
Rated current 60°C	5.2 A
Rated current 65°C	5.1 A
Rated current 70°C	5 A
Rated short-circuit breaking capacity I_{cn} under 230 V AC according to IEC 61009-1	6 kA
Breaking and opening capacity I_{dm}	3 kA
Rated residual operating current I_{dn}	30 mA

Architecture

Curve	C
Type of pole	1P+N

Installation, mounting

Nominal tightening torque top terminal	2.40 - 2.40 Nm
Nominal tightening torque down terminal	3.50 - 3.50 Nm
Type of bottom connection for modular devices	biconnect
Type of top connection for modular devices	Screw terminal

Main electrical attributes

Rated short-circuit breaking capacity Icn AC according to IEC 60898-1	6 kA
Safety	
Residual current type	A
Voltage	
Rated insulation voltage Ui	400 V
Rated impulse withstand voltage Uimp	4,000 V
Rated operational voltage Ue	230 - 230 V
Power	
Total power loss under IN	2.69 W
Use conditions	
Class of energy limitation I²t	3
Operating temperature	-25 - 70 °C
Storage/transport temperature	-25 - 80 °C
Endurance	
Number of mechanical operations	8,000
Electric endurance in number of cycles	2,000
Capacity	
Number of modules	1
Dimensions	
Height	125 mm
Width	17.50 mm
Depth	70 mm
Frequency	
Frequency	50 - 50 Hz