



ARL982U

RCBO with dangerous arc detection 1M 32A C curve 6kA Type A 30mA LFL 1m

Technical characteristics

Electric current

Rated current	32 A
Rated current -25°C	38.60 A
Rated current at -20°C	38 A
Rated current -15°C	37.40 A
Rated current -5°C	36.20 A
Rated current at 0°C	35.60 A
Rated current 5°C	35 A
Rated current 10°C	34.40 A
Rated current 15°C	33.80 A
Rated current at 20°C	33.20 A
Rated current 25°C	32.60 A
Rated current 35°C	31.30 A
Rated current at 40°C	30.70 A
Rated current at 45°C	30 A
Rated current 55°C	28.60 A
Rated current 60°C	28 A
Rated current 65°C	27.30 A
Rated current 70°C	26.60 A
Breaking and opening capacity I_{dm}	3 kA
Rated residual operating current I_{dn}	30 mA

Architecture

Curve	C
Type of pole	1P+N

Main electrical attributes

Rated short-circuit breaking capacity I_{cn} AC according to IEC 60898-1	6 kA
Nominal tightening torque top terminal	2.40 - 2.40 Nm
Nominal tightening torque down terminal	3.50 - 3.50 Nm

Safety

Residual current type	A
-----------------------	---

Voltage

Rated insulation voltage U_i	400 V
Rated impulse withstand voltage U_{imp}	4,000 V

Use conditions

Class of energy limitation I ² t	3
Operating temperature	-25 - 70 °C
Storage/transport temperature	-25 - 80 °C
Endurance	
Number of mechanical operations	8,000
Electric endurance in number of cycles	2,000
Capacity	
Number of modules	1
Installation, mounting	
Type of bottom connection for modular devices	biconnect
Type of top connection for modular devices	Screw terminal
Dimensions	
Height	125 mm
Width	17.50 mm
Depth	70 mm