



CDC490

RCCB 4P 125A 30mA AC Class

Technical characteristics

Architecture

Neutral position	right
Number of poles	4 P
Fixing mode	Din-Rail

Main electrical features

Frequency	50 Hz
-----------	-------

Electric current

Rated residual operating current	30 mA
Rated conditional short-circuit current I_{nc} according to EN 61008-1	6 kA

Dimensions

Depth of installed product	68 mm
Height of installed product	85 mm
Width of installed product	71 mm

Power

Total power loss under I_N	33.6 W
------------------------------	--------

Tripping

Short-time delayed tripping	No
-----------------------------	----

Endurance

Electric endurance in number of cycles	2000
Number of mechanical operations	10000

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

Protection index IP	IP20
Residual current type	AC

Use conditions

Operating temperature	-5...40 °C
-----------------------	------------