



ARM916U

MCB with dangerous arc detection 1M 16A B curve 6kA

Technical characteristics

Electric current

Rated current	16 A
Rated current -25°C	20.50 A
Rated current at -20°C	20.10 A
Rated current -15°C	19.70 A
Rated current -10°C	19.30 A
Rated current -5°C	18.90 A
Rated current at 0°C	18.50 A
Rated current 5°C	18.10 A
Rated current 10°C	17.60 A
Rated current 15°C	17.20 A
Rated current at 20°C	16.80 A
Rated current 25°C	16.40 A
Rated current 30°C	16 A
Rated current 35°C	15.70 A
Rated current at 40°C	15.50 A
Rated current at 45°C	15.20 A
Rated current at 50°C	15 A
Rated current 55°C	14.70 A
Rated current 60°C	14.50 A

Architecture

Curve	B
Type of pole	1P+N

Main electrical attributes

Rated short-circuit breaking capacity I _{cn} AC according to IEC 60898-1	6 kA
Nominal tightening torque top terminal	2.40 - 2.40 Nm
Nominal tightening torque down terminal	3.50 - 3.50 Nm

Voltage

Rated insulation voltage U _i	400 V
Rated impulse withstand voltage U _{imp}	4,000 V

Power

Total power loss under I _N	3.82 W
---------------------------------------	--------

Use conditions

Class of energy limitation I ² t	3
---	---

Operating temperature	-25 - 70 °C
Storage/transport temperature	-25 - 80 °C
Endurance	
Number of mechanical operations	8,000
Electric endurance in number of cycles	2,000
Installation, mounting	
Type of bottom connection for modular devices	biconnect
Type of top connection for modular devices	Screw terminal
Capacity	
Number of modules	1
Dimensions	
Height	125 mm
Width	17.50 mm
Depth	70 mm