

CDF540U

**RCCB 1P+N 40A 30mA F**

**Technical characteristics**

**Architecture**

Neutral position	right
Number of poles	2 P
Type of pole	1P+N

**Main electrical features**

Rated operational voltage Ue	230 V
Frequency	50 Hz
Type of supply voltage	AC

**Voltage**

Rated insulation voltage	500 V
Max operating voltage	253 V
Rated impulse withstand voltage	4000 V

**Electric current**

Rated residual operating current	30 mA
Rated conditional short-circuit current Inc according to EN 61008-1	10 kA

**Electric current / temperature**

Rating current 30°C	40 A
---------------------	------

**Dimensions**

Depth of installed product	70 mm
Height of installed product	85 mm
Width of installed product	36 mm

**Power**

Total power loss under IN	3.31 W
---------------------------	--------

**Tripping**

Short-time delayed tripping	Yes
-----------------------------	-----

**Endurance**

Electric endurance in number of cycles	10000
Number of mechanical operations	20000

**Equipment**

Quick connect	no
Can be accessorized	Yes

**Standards**

Standard text	EN 61008-1
European directive WEEE	concerned

**Safety**

Protection index IP	IP20
Residual current type	F

**Use conditions**

Operating temperature	-25...70 °C
-----------------------	-------------