



CEA240U

## RCCB 2P 40A 100mA A Class

### Technical characteristics

#### Architecture

Neutral position	right
Number of poles	2 P

#### Main electrical features

Rated operational voltage Ue	230 V
Frequency	50 Hz

#### Voltage

Rated insulation voltage	500 V
Rated impulse withstand voltage	4000 V

#### Electric current

Rated residual operating current	100 mA
Rated conditional short-circuit current Inc according to EN 61008-1	6 kA

#### Electric current / temperature

Rating current 30°C	40 A
---------------------	------

#### Dimensions

Depth of installed product	70 mm
Height of installed product	83 mm
Width of installed product	35 mm

#### Power

Total power loss under IN	3.2 W
---------------------------	-------

#### Tripping

Short-time delayed tripping	No
-----------------------------	----

#### Endurance

Electric endurance in number of cycles	2000
Number of mechanical operations	4000

#### Installation, mounting

Tightening torque	2,8Nm
-------------------	-------

#### Connection

Connection cross-sect. flexible conductor	1 / 16mm <sup>2</sup>
Connection cross-sect. rigid cable	1 / 25mm <sup>2</sup>
Type of connection	with screw

**Standards**

---

Standard text

BS 61008-1 ; EN 61008-1

**Safety**

---

Residual current type

A

**Use conditions**

---

Operating temperature

-25...40 °C