



CEA240U

**RCCB 2P 40A 100mA A Class**

**Technical characteristics**

**Architecture**

Neutral position	right
Number of poles	2 P
Fixing mode	DIN rail type O (symmetrical)

**Main electrical features**

Rated operational voltage Ue	230 V
Frequency	50 Hz

**Voltage**

Rated insulation voltage	500 V
Rated impulse withstand voltage	4000 V

**Electric current**

Rated residual operating current	100 mA
Rated conditional short-circuit current Inc according to EN 61008-1	6 kA

**Electric current / temperature**

Rating current 30°C	40 A
---------------------	------

**Dimensions**

Depth of installed product	70 mm
Height of installed product	83 mm
Width of installed product	35 mm

**Power**

Total power loss under IN	3.2 W
---------------------------	-------

**Tripping**

Short-time delayed tripping	No
-----------------------------	----

**Endurance**

Electric endurance in number of cycles	2000
Number of mechanical operations	4000

**Installation, mounting**

Tightening torque	2,8Nm
-------------------	-------

**Connection**

Connection cross-sect. flexible conductor	1 / 16mm <sup>2</sup>
Connection cross-sect. rigid cable	1 / 25mm <sup>2</sup>

Type of connection

with screw

---

**Standards**

Standard text

BS 61008-1 ; EN 61008-1

European directive WEEE

concerned

---

**Safety**

Protection index IP

IP20

Residual current type

A

---

**Use conditions**

Operating temperature

-25...40 °C