



CF463J

## RCCB 4P 63A 300mA A Class

### Technical characteristics

#### Architecture

Type of pole	3P+N
--------------	------

#### Electric current

Rated current	63 A
Rated residual operating current $I_{dn}$	300 mA
Breaking and opening capacity $I_{dm}$	1.50 kA
Rated conditional short-circuit current $I_{nc}$ according to EN61008-1	6 kA
Rated current -25°C	63 A
Rated current at -20°C	63 A
Rated current -15°C	63 A
Rated current -10°C	63 A
Rated current -5°C	63 A
Rated current at 0°C	63 A
Rated current 5°C	63 A
Rated current 10°C	63 A
Rated current 15°C	63 A
Rated current at 20°C	63 A
Rated current 25°C	63 A
Rated current 30°C	63 A
Rated current 35°C	63 A
Rated current at 40°C	63 A
Rated current at 45°C	60 A
Rated current at 50°C	58 A
Rated current 55°C	55 A
Rated current 60°C	51 A
Rated current 65°C	48 A
Rated current 70°C	45 A

#### Installation, mounting

Nominal tightening torque top terminal	2.80 - 2.80 Nm
Nominal tightening torque down terminal	2.80 - 2.80 Nm
Type of top connection for modular devices	Screw terminal
Type of bottom connection for modular devices	biconnect
Nominal tightening torque	2.80 - 2.80 Nm

#### Voltage

Rated operational voltage Ue	230 - 400 V
Type voltage supply	AC
Rated insulation voltage Ui	500 V
Rated impulse withstand voltage Uimp	4,000 V
Max. operating voltage	440 V
<b>Frequency</b>	
Frequency	50 - 50 Hz
<b>Capacity</b>	
Number of modules	4
<b>Compatibility</b>	
Suitable for DIN Rail	Yes
<b>Safety</b>	
Residual current type	A
Ingress Protection (IP) class	IP20
<b>Connection</b>	
Cross-section of input and output with screws, for massive conductors	1 - 25 mm²
Cross-section of input and output with screws, for flexible conductors	1 - 16 mm²
Cross-section flexible conductor	16 mm²
Cross-section rigid conductor	25 mm²
<b>Power</b>	
Total power loss under IN	19.70 W
<b>Use conditions</b>	
Max. Altitude	2,000 m
<b>Endurance</b>	
Electric endurance in number of cycles	2,000
Number of mechanical operations	4,000
<b>Connectivity</b>	
Type of connection	Screw terminal
Top connection alignment for modular devices	Aligned terminal
Down connection alignment for modular devices	Aligned terminal
<b>Dimensions</b>	
Height	83 mm
Width	70 mm
Depth	70 mm