



CN487U

RCCB 4P 100A 100mA A S

Technical characteristics

Architecture

Neutral position	right
Number of poles	4 P
Type of pole	3P+N

Main electrical features

Frequency	50 Hz
Type of supply voltage	AC

Voltage

Rated impulse withstand voltage	4000 V
---------------------------------	--------

Electric current

Rated residual operating current	100 mA
Rated conditional short-circuit current I_{nc} according to EN 61008-1	6 kA

Electric current / temperature

Rating current 30°C	100 A
---------------------	-------

Dimensions

Depth of installed product	70 mm
Height of installed product	86 mm
Width of installed product	70 mm

Power

Total power loss under IN	30.2 W
---------------------------	--------

Tripping

Short-time delayed tripping	Yes
-----------------------------	-----

Endurance

Electric endurance in number of cycles	2000
Number of mechanical operations	4000

Installation, mounting

Tightening torque	3,3Nm
-------------------	-------

Connection

Type of connection	with screw
--------------------	------------

Equipment

Can be accessorized

Yes

Standards

Standard text

EN 61008-1

Safety

Residual current type

A SEL

Use conditions

Operating temperature

-25...40 °C