



CNA584U

RCCB 1P+N 100A 100mA A S

Technical characteristics

Architecture

Neutral position	right
Number of poles	2 P
Type of pole	1P+N
Fixing mode	DIN rail type O (symmetrical)

Main electrical features

Rated operational voltage U_e	230 V
Frequency	50 Hz
Type of supply voltage	AC

Voltage

Rated insulation voltage	500 V
Max operating voltage	253 V
Rated impulse withstand voltage	4000 V

Electric current

Rated residual operating current	100 mA
Rated conditional short-circuit current I_{nc} according to EN 61008-1	10 kA

Electric current / temperature

Rating current 30°C	100 A
---------------------	-------

Dimensions

Depth of installed product	70 mm
Height of installed product	85 mm
Width of installed product	36 mm

Power

Total power loss under IN	13.89 W
---------------------------	---------

Tripping

Short-time delayed tripping	Yes
-----------------------------	-----

Endurance

Electric endurance in number of cycles	10000
Number of mechanical operations	20000

Equipment

Quick connect	no
---------------	----

Can be accessorized

Yes

Standards

Standard text

EN 61008-1

European directive WEEE

concerned

Safety

Protection index IP

IP20

Residual current type

A SEL

Use conditions

Operating temperature

-25...50 °C