



EC100

## Hours counter

### Technical characteristics

#### Architecture

Fixing mode Din-Rail

#### Main electrical features

Frequency 50 Hz

#### Dimensions

Depth of installed product 60 mm

Height of installed product 90 mm

Width of installed product 35 mm

#### Power

Total power loss under IN 1.5 W

#### Installation, mounting

Mounting type din-Rail

#### Safety

Protection index IP IP20

#### Use conditions

Operating temperature -10...45 °C