



BDA263

Earth leakage add-on block 2P 63A 30mA A Class

Technical characteristics

Architecture

Neutral position	right
Number of poles	2 P
Type of pole	2 P
Fixing mode	DIN rail type O (symmetrical)

Main electrical features

Rated operational voltage Ue	230 V
Frequency	50 Hz

Voltage

Rated insulation voltage	500 V
Rated impulse withstand voltage	4000 V

Electric current

Rated residual operating current	30 mA
----------------------------------	-------

Dimensions

Depth of installed product	92 mm
Height of installed product	70 mm
Width of installed product	4.4 cm

Power

Total power loss under IN	18 W
---------------------------	------

Tripping

Short-time delayed tripping	No
-----------------------------	----

Endurance

Electric endurance in number of cycles	1000
Number of mechanical operations	1000

Connection

Connection cross-sect. flexible conductor	16mm ²
---	-------------------

Standards

Standard text	EN 61009-1
European directive WEEE	concerned

Safety

Protection index IP	IP2X
---------------------	------

Residual current type

A

Use conditions

Operating temperature

-25...70 °C