



EC100

## Hours counter

### Technical characteristics

#### Main electrical features

|           |       |
|-----------|-------|
| Frequency | 50 Hz |
|-----------|-------|

#### Dimensions

|                             |       |
|-----------------------------|-------|
| Depth of installed product  | 60 mm |
| Height of installed product | 90 mm |
| Width of installed product  | 35 mm |

#### Power

|                           |       |
|---------------------------|-------|
| Total power loss under IN | 1.5 W |
|---------------------------|-------|

#### Power supply

|                |               |
|----------------|---------------|
| Supply voltage | 230 V +/- 15% |
|----------------|---------------|

#### Installation, mounting

|               |          |
|---------------|----------|
| Mounting type | din-Rail |
|---------------|----------|

#### Connection

|   |                         |
|---|-------------------------|
| Connection cross-sect. flexible conductor | 1 / 6mm <sup>2</sup>    |
| Connection cross-sect. rigid cable        | 1,5 / 10mm <sup>2</sup> |
| Type of connection                        | with screw              |

#### Use conditions

|                       |             |
|-----------------------|-------------|
| Operating temperature | -10...45 °C |
|-----------------------|-------------|