



BE464

Earth leakage add-on block 4P 63A 100mA AC Class

Technical characteristics

Architecture

Neutral position	left
Number of poles	4 P

Main electrical features

Rated operational voltage Ue	230 / 400 V
Frequency	50 Hz

Voltage

Rated insulation voltage	500 V
Rated impulse withstand voltage	4000 V

Electric current

Rated residual operating current	100 mA
----------------------------------	--------

Dimensions

Depth of installed product	9.2 cm
Height of installed product	7 cm
Width of installed product	3.5 cm

Power

Total power loss under IN	35.5 W
---------------------------	--------

Tripping

Short-time delayed tripping	No
-----------------------------	----

Endurance

Electric endurance in number of cycles	2000
Number of mechanical operations	1000

Installation, mounting

Tightening torque	2,8Nm
-------------------	-------

Connection

Connection cross-sect. flexible conductor	16mm ²
Connection cross-sect. rigid cable	25mm ²

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

Protection index IP	IP20
---------------------	------

Residual current type

AC

Use conditions

Operating temperature

-5...40 °C