



EC100

## Hours counter

### Technical characteristics

#### Architecture

Fixing mode	Din-Rail
-------------	----------

#### Main electrical features

Frequency	50 Hz
-----------	-------

#### Dimensions

Depth of installed product	60 mm
Height of installed product	90 mm
Width of installed product	35 mm

#### Power

Total power loss under IN	1.5 W
---------------------------	-------

#### Power supply

Supply voltage	230 V +/- 15%
----------------	---------------

#### Installation, mounting

Mounting type	din-Rail
---------------	----------

#### Connection

Connection cross-sect. flexible conductor	1 / 6mm <sup>2</sup>
Connection cross-sect. rigid cable	1,5 / 10mm <sup>2</sup>
Type of connection	with screw

#### Safety

Protection index IP	IP20
---------------------	------

#### Use conditions

Operating temperature	-10...45 °C
-----------------------	-------------