



BEA263

## Earth leakage add-on block 2P 63A 100mA A Class

### Technical characteristics

#### Architecture

Neutral position	right
Number of poles	2 P
Type of pole	2 P
Fixing mode	DIN rail type O (symmetrical)

#### Main electrical features

Rated operational voltage Ue	230 / 400 V
Frequency	50 Hz

#### Voltage

Rated insulation voltage	500 V
Rated impulse withstand voltage	4000 V

#### Electric current

Rated residual operating current	100 mA
----------------------------------	--------

#### Dimensions

Depth of installed product	92 mm
Height of installed product	70 mm
Width of installed product	3.5 cm

#### Power

Total power loss under IN	18 W
---------------------------	------

#### Tripping

Short-time delayed tripping	No
-----------------------------	----

#### Endurance

Electric endurance in number of cycles	2000
Number of mechanical operations	2000

#### Connection

Connection cross-sect. flexible conductor	16mm <sup>2</sup>
---	-------------------

#### Standards

Standard text	EN 61009-1
European directive WEEE	concerned

#### Safety

Protection index IP	IP2X
---------------------	------

Residual current type

A

**Use conditions**

---

Operating temperature

-25...70 °C