



BEA463

**Earth leakage add-on block 4P 63A 100mA A Class**

**Technical characteristics**

**Architecture**

Neutral position	right
Number of poles	4 P
Type of pole	4 P

**Main electrical features**

Rated operational voltage Ue	230 / 400 V
Frequency	50 Hz

**Voltage**

Rated insulation voltage	500 V
Rated impulse withstand voltage	4000 V

**Electric current**

Rated residual operating current	100 mA
----------------------------------	--------

**Dimensions**

Depth of installed product	92 mm
Height of installed product	70 mm
Width of installed product	3.5 cm

**Power**

Total power loss under IN	35.5 W
---------------------------	--------

**Tripping**

Short-time delayed tripping	No
-----------------------------	----

**Endurance**

Electric endurance in number of cycles	2000
Number of mechanical operations	2000

**Installation, mounting**

Tightening torque	2,9Nm
-------------------	-------

**Connection**

Connection cross-sect. flexible conductor	16mm <sup>2</sup>
Connection cross-sect. rigid cable	25mm <sup>2</sup>

**Standards**

Standard text	EN 61009-1
---------------	------------

**Safety**

**Use conditions**

---

Operating temperature

-25...70 °C