


BFC480E



**Earth leakage add-on-block 4P 125A 300mA type AC**

**Technical characteristics**

**Architecture**

Neutral position	Left or right
Number of poles	4 P

**Main electrical features**

Rated operational voltage Ue	240 / 415 V
Frequency	50 Hz

**Voltage**

Rated insulation voltage	500 V
Rated impulse withstand voltage	6000 V

**Electric current**

Rated residual operating current	300 mA
----------------------------------	--------

**Electric current / temperature**

Rating current 30°C	125 A
---------------------	-------

**Dimensions**

Depth of installed product	69 mm
Height of installed product	103 mm
Width of installed product	213 mm

**Power**

Total power loss under IN	15 W
---------------------------	------

**Tripping**

Short-time delayed tripping	No
-----------------------------	----

**Endurance**

Electric endurance in number of cycles	1000
Number of mechanical operations	7000

**Installation, mounting**

Tightening torque	3,5Nm
-------------------	-------

**Standards**

Standard text	IEC 61009-1 ; EN 61009-1
European directive WEEE	concerned

**Safety**

Protection index IP	IP20
---------------------	------

