



BPA263

Earth leakage add-on block 2P 63A 300mA A S Class

Technical characteristics

Architecture

Neutral position	right
Number of poles	2 P
Type of pole	2 P
Fixing mode	DIN rail type O (symmetrical)

Main electrical features

Rated operational voltage Ue	230 / 400 V
Frequency	50 Hz

Voltage

Rated insulation voltage	500 V
Rated impulse withstand voltage	4000 V

Electric current

Rated residual operating current	300 mA
----------------------------------	--------

Dimensions

Depth of installed product	92 mm
Height of installed product	70 mm
Width of installed product	3.5 cm

Power

Total power loss under IN	66 W
---------------------------	------

Tripping

Short-time delayed tripping	Yes
-----------------------------	-----

Endurance

Electric endurance in number of cycles	2000
Number of mechanical operations	2000

Connection

Connection cross-sect. flexible conductor	16mm ²
---	-------------------

Standards

Standard text	EN 61009-1
European directive WEEE	concerned

Safety

Protection index IP	IP2X
---------------------	------

Residual current type

A SEL

Use conditions

Operating temperature

-25...70 °C