




EE820



IP55

Motion detector Infrared 140°, IP55, wall mounted, white

Technical characteristics

Architecture

Bus system	Without
Fixing mode	surface-mounting

Functions

Function	can only be used as individual unit
----------	-------------------------------------

Main electrical features

Rated operational voltage Ue	230 V
Frequency	50/60 Hz

Dimensions

Height of installed product	2.5 m
-----------------------------	-------

Power supply

Supply voltage	230 V +10% / -15%
----------------	-------------------

Detection

Detection angle	140 °
-----------------	-------

Materials

Colour	white
RAL colour	RAL 9010 - Pure white
Material	plastic

Lighting control

Brightness measurement range	5 / 1000 Lux
------------------------------	--------------

Installation, mounting

Maximum Mounting Height	4 m
-------------------------	-----

Connection

Type of connection	with plug-in terminals
--------------------	------------------------

Settings

Setting	with potentiometers for setting the response brightness and delay time without dismantling
---------	--

Scope of delivery

Component	with fitting material
-----------	-----------------------

Equipment

Angle of horizontal detection	140 °
-------------------------------	-------

Safety

Protection index IP

IP55

Use conditions

Operating temperature

-20...55 °C