



EE820



Motion detector Infrared 140°, IP55, wall mounted, white

Technical characteristics

Architecture

Bus system Without

Functions

Function can only be used as individual unit

Main electrical features

Rated operational voltage Ue 230 V

Frequency 50/60 Hz

Dimensions

Height of installed product 2.5 m

Power supply

Supply voltage 230 V +10% / -15%

Detection

Detection angle 140 °

Materials

Colour white

RAL colour RAL 9010 - Pure white

Material plastic

Lighting control

Brightness measurement range 5 / 1000 Lux

Installation, mounting

Maximum Mounting Height 4 m

Connection

Type of connection with plug-in terminals

Settings

Setting with potentiometers for setting the response brightness and delay time without dismantling

Scope of delivery

Component with fitting material

Equipment

Angle of horizontal detection 140 °

Use conditions

Operating temperature

-20...55 °C