



CD283U

RCCB 2P 80A 30mA A

Technical characteristics

Architecture

Neutral position	right
Number of poles	2 P
Type of pole	1P+N

Main electrical features

Frequency	50 Hz
Type of supply voltage	AC

Voltage

Rated impulse withstand voltage	4000 V
---------------------------------	--------

Electric current

Rated residual operating current	30 mA
Rated conditional short-circuit current I_{nc} according to EN 61008-1	6 kA

Electric current / temperature

Rating current 30°C	80 A
---------------------	------

Dimensions

Depth of installed product	70 mm
Height of installed product	83 mm
Width of installed product	35 mm

Power

Total power loss under I_N	9.1 W
------------------------------	-------

Tripping

Short-time delayed tripping	No
-----------------------------	----

Endurance

Electric endurance in number of cycles	2000
Number of mechanical operations	4000

Installation, mounting

Tightening torque	3,3Nm
-------------------	-------

Connection

Type of connection	with screw
--------------------	------------

Equipment

Can be accessorized

Yes

Standards

Standard text

EN 61008-1

Safety

Residual current type

A

Use conditions

Operating temperature

-25...40 °C